

Laboratory Wringer



To evenly squeeze or extract excess liquid from fabrics

12" (300 mm) working width with neoprene rollers 2 1/8" (54 mm) diameter. Drive speed 2.5 mm (1") per second. Dead weight loading up to 105 lb (50 kg) x 5 lb (2.3 kg).

Standards

AATCC 92

Ordering Information

D394 Crumpleflex Tester
400920 Optional Liquor Trough



SDL ATLAS LLC
3934 Airway Drive
Rock Hill, SC 29732-9200, USA
Telephone: +1 803 329 2110
Facsimile: +1 803 329 2133
Website: www.sdatlas.com

SDL ATLAS LTD.
1/F (South-East) & 2F, Shenjian Mansion,
Central District (West), Hi-Tech Park,
Nanshan, Shenzhen, 518057, P.R.C.
Telephone: +86 (755) 2671 1168
Facsimile: +86 (755) 2671 1337
Website: www.sdatlas.com

SDL ATLAS LTD.
3J, Garment Centre, 576 Castle Peak Road,
Kowloon, Hong Kong.
Telephone: (852) 3443 4888
Facsimile: (852) 3443 4999
Website: www.sdatlas.com